



Protective Carrying Cases

Hard-Sided, Leather and Vinyl Sleeve Varieties





Visit omega.co.uk
for More Information
on Omega's Wide
Selection of Quality
Instrument Cases!

SC737
£670



SC67
£670




SC546, SC-HHLM3, SC74
£670



SC-SM
£670



ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)			
Model No.	Price	Dimensions (mm)	Description
130001	£137.00	330 x 458 x 152	Zero aluminium case with combo lock
SC-530	43.50	203 x 115 x 45	Soft case with belt loop and shoulder strap
SC-531	43.50	146 x 89 x 64	Soft case with belt loop
SC-540	43.50	140 x 96 x 70	Soft case with belt loop
RCC-1100	57.00	432 x 305 x 140	Rugged carrying case with foam insert
RCC-200A	28.00	356 x 254 x 89	Rugged carrying case with foam insert
RCC-6500	27.00	216 x 140 x 64	Soft leather case with belt loop and shoulder strap
SC-83	20.00	134 x 58 x 25	Soft case with belt loop
RCC-1000	13.50	318 x 229 x 115	Rugged carrying case with foam insert
SC-600	13.50	229 x 165 x 32	Soft case with belt loop
SC-HH11A	10.00	229 x 64 x 38	Soft case with belt loop and mounting magnet
SC-HHM20	10.00	229 x 102 x 45	Soft case with belt loop
SC-50	8.70	185 x 95 x 32	Soft case with belt loop
SC-300A	8.40	102 x 127 x 83	Soft case with belt loop
SC-450L	8.00	235 x 83 x 45	Soft case with belt loop and hook
SC-560	8.00	178 x 51 x 38	Gun-style holster case with belt loop
SC-HH500	8.00	203 x 51 x 89	Soft case with belt loop
SC-450S	6.70	152 x 76 x 38	Soft case with belt loop and hook
SC546	6.70	165 x 51 x 25	Soft case
SC67	6.70	127 x 51 x 38	Soft case
SC737	6.70	133 x 95 x 38	Soft case with shoulder strap and belt clip
SC74	6.70	140 x 51 x 25	Soft case
SC-800	6.70	178 x 89 x 58	Soft case with belt loop
SC-HHLM3	6.70	152 x 51 x 19	Soft case
SC-SM	6.70	216 x 89 x 64	Soft case with belt loop

Ordering Example: 130001, zero aluminium case with combo lock, £137.

SC-450S, SC-800
£670



SC-450L
£8



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters