

Rugged Bulb and Capillary Thermostats

AR Series
Starts at
\$235



- ✓ Bulb and Capillary Design
- ✓ Long-Lasting, Snap-Action Mechanism
- ✓ Double-Pole, Single-Throw Contacts
- ✓ 3 Different Bulb Styles Available
- ✓ Optional Knob Cover and Pilot Light

Specifications

Temperature Range: -20 to 370°C (-4 to 698°F)

Operating Voltage:
Single-Phase: 120 to 480V
3-Phase: 120 to 277V

Enclosure: General purpose


Contacts: DPST, open on temperature rise; at positive off position, contacts cannot close

Differential: ±4% of scale

Bulb and Capillary: Copper for units rated at 120°C (248°F) and lower; nickel-plated copper for units between 95°C (203°F) and 290°C (504°F); tin-plated steel for units between 150°C (302°F) and 370°C (698°F)

Weight:

AR and ARR Series: 1.14 kg (2.5 lb)
AR-LT and AR-EP Series: 2.27 kg (5 lb)



Typical Applications

- ✓ Temperature Control of Any Electrically Heated Solid, Liquid or Gas
- ✓ Excellent for Ovens or Sterilizers
- ✓ Molding Machines
- ✓ Heat Exchangers
- ✓ Labeling Machines
- ✓ Water Baths
- ✓ Heat Sealers
- ✓ May Be Used to Control Refrigerating, Ventilating, and Alarm Systems

These thermostats use sensitive bulbs that can be used in confined locations. Styles 4 and 5 bulbs are designed for inserting in drilled holes in platens and dies or for direct immersion.

Sensors for air and pipeline heating applications (style 9) can be coiled to inside radii as small as 13 mm (½").

CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model Number	Price	Temp Range °C (°F)	Amp Rating		Bulb Style	Dimensions (in)		Cap (ft) Lgth.
			120 to 277V	480V		Dia.	Lgth.	
Single-Phase AR								
AR-115	\$235	-20 to 40 (-4 to 104)	30	10	5	3/8	3 7/8	7
AR-115A	235	-20 to 40 (-4 to 104)	30	10	5	3/8	3 7/8	2
AR-115C	250	-20 to 40 (-4 to 104)	30	10	5	3/8	3 7/8	12
AR-214	235	10 to 120 (59 to 248)	30	10	4	1/4	5 5/32	7
AR-214D	250	10 to 120 (59 to 248)	30	10	4	1/4	5 5/32	15
AR-215	235	10 to 120 (59 to 248)	30	10	5	3/8	4	7
AR-215A	235	15 to 120 (59 to 248)	30	10	5	3/8	4	2
AR-219	250	15 to 120 (59 to 248)	30	10	9	3/16	10 3/4	7
AR-219D	235	15 to 120 (59 to 248)	30	10	9	3/16	10 3/4	15
AR-514	235	95 to 290 (200 to 550)	30	10	4	1/4	5 5/8	7
AR-519	235	95 to 290 (200 to 550)	30	10	9	3/16	9	7
AR-519D	235	95 to 290 (200 to 550)	30	10	9	3/16	9	15
AR-715	235	150 to 370 (302 to 698)	30	10	5	3/8	3 1/16	7
AR-719	235	150 to 370 (302 to 698)	30	10	9	3/16	11 13/16	7
3-Phase AR-3								
AR-2153	\$290	10 to 120 (59 to 248)	30**	-	5	3/8	4 1/4	7
Single-Phase ARR (Inverse Action)								
ARR-215	\$250	10 to 120 (59 to 248)	30	-	5	3/8	4 1/4	7
ARR-219	235	10 to 120 (59 to 248)	30	-	9	3/16	16 9/32	7
ARR-519	207	95 to 290 (200 to 550)	30	-	9	3 3/16	11 1/4	7

Comes complete with operator's manual.

**120 to 250V.

To order any unit with optional knob cover, add suffix "-KC" to model number, and \$16 to price. To order any unit above with optional pilot light, add suffix "-P" to model number and call for price.

Ordering Examples: AR-115KC, single-phase AR thermostat, temperature range -20 to 40°C (-4 to 104°F), style 5 bulb, with optional knob cover, \$250 + 16 = \$266.

AR-719, single phase AR thermostat, 150 to 370°C (302 to 698°F) temperature range, style 9 bulb, \$235.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters