


BX

Extension Grade
Copper/Copper
Duplex
ANSI Type BX



ANSI
color
code
shown

To order
IEC color
code see
page A-9

Compensating Extension Wires for Platinum 6% Rhodium (-)/Platinum 30% Rhodium (+)
Thermocouples ANSI Color Code: Positive Wire, Gray; Negative Wire, Red; Overall, Gray**

**MOST POPULAR
MODELS HIGHLIGHTED!**

Insulation	AWG No.	Model Number	Price/1000'	Type Wire	Insulation		Max Temp*		Nominal Size: mm (in)	Wt. kg/300 m (lb/1000')†
					Conductor	Overall	°C	°F		
Glass	20	EXGG-B-20	\$390	Solid	Glass braid	Glass braid	100	212	1.5 x 2.4 (0.060 x 0.095)	4 (9)
PFA	26	EXTT-B-26S	400	7 x 34	PFA	PFA	100	212	1.1 x 1.7 (0.042 x 0.068)	4 (9)
Polyvinyl	24	EXPP-B-24	235	Solid	Polyvinyl	Polyvinyl	100	212	1.9 x 3.1 (0.075 x 0.120)	2 (5)
	24	EXPP-B-24S	370	7 x 32	Polyvinyl	Polyvinyl	100	212	2.2 x 3.4 (0.182 x 0.134)	5 (12)
FEP	26	EXFF-B-26S	345	7 x 34	FEP	FEP	100	212	1.1 x 1.7 (0.042 x 0.068)	2 (5)

* Maximum temperature is for extension-grade wire or insulation, whichever is lower.

** Black on EXGG wire.

† Weight of spool and wire, rounded to next highest kg (lb) (does not include packing material).

Ordering Example: EXGG-B-20-25, 25' spool of extension grade thermocouple wire, Type BX, 20 gage, stranded, glass insulation, \$390 x 0.0625 = \$25.

CX

Extension Grade
W5%Re/W26%Re
Duplex
Type CX



Compensating Extension Wires for W5%Re/W26%Re Thermocouples Color Code:
For EXGG Wire, Positive Wire, White/Red Trace; Negative Wire, Red; Overall, White/Red Trace
For EXXT Wire, Positive Wire, White; Negative Wire, White/Red Trace; Overall, White/Red Trace

Insulation	AWG No.	Model Number	Price/1000'	Type Wire	Insulation		Max Temp*		Nominal Size: mm (in)	Wt. kg/300 m (lb/1000')†
					Conductor	Overall	°C	°F		
Nextel Ceramic*	24	EXXC-C-24	\$1750	Solid	Ceramic	Ceramic	427	800	2.9 x 4.4 (0.115 x 0.175)	5 (12)
	24	EXXT-C-24	1585	Solid	Ceramic	Ceramic	427	800	2.2 x 3.4 (0.088 x .0132)	5 (11)
	24	EXXL-C-24	1425	Solid	Ceramic	Ceramic	427	800	2.0 x 3.0 (0.078 x 0.116)	5 (10)
Glass	24	EXGG-C-24	650	Solid	Glass braid	Glass braid	427	800	1.3 x 2.0 (0.050 x 0.080)	3 (7)

Note: The XC is the standard braid, XT is a tight braid and XL is a light-duty braid; the three types of braid affect only the amount of Nextel used in manufacturing.


* Maximum temperature is for extension-grade wire or insulation, whichever is lower.

† Weight of spool and wire, rounded to next highest kg/lb (does not include packing material).

‡ Has color tracers on jacket and conductors.

Ordering Example: EXGG-C-24-25, 25' spool of extension-grade thermocouple wire, Type CX, 24 gage, stranded, glass insulation, \$650 x 0.0625 = \$41.

Thermistor and RTD Extension Wire



Nickel-Plated Copper Wire***

Color Code: 2 Cu-Rd/Bk^{†††}; 3 Cu-Rd/Bk/Bk; 4 Cu-Rd/Rd/Bk/Bk

Insulation	AWG No.	Model Number	Price/1000'	# of Con.	Type Wire	Insulation		Max Temp*		Nominal Size: mm (in)	Wt. kg/300 m (lb/1000')†
						Conductor	Overall	°C	°F		
Glass	20	EXGG-2CU-20	\$370	2	Solid	Glass braid	Glass braid	482	900	1.5 x 2.4 (0.060 x 0.095)	4 (9)
	26	EXGG-2CU-26S	280	2	7 x 34	Glass braid	Glass braid	482	900	1.5 x 1.3 (0.060 x 0.052)	2 (5)
	26	EXGG-3CU-26S	360	3	7 x 34	Glass braid	Glass braid	482	900	1.5 x 1.6 (0.060 x 0.064)	3 (7)
	26	EXGG-4CU-26S	420	4	7 x 34	Glass braid	Glass braid	482	900	1.5 x 1.7 (0.060 x 0.066)	4 (9)
Neoflon PFA	26	EXTT-2CU-26S	480	2	7 x 34	PFA	PFA	260	500	1.1 x 1.7 (0.042 x 0.068)	2 (5)
	26	EXTT-3CU-26S	650	3	7 x 34	PFA	PFA	260	500	1.8 Ø (0.072 Dia.)	4 (9)
	26	EXTT-4CU-26S	700	4	7 x 34	PFA	PFA	260	500	2.1 Ø (0.082 Dia.)	4 (9)
Polyvinyl	24	EXPP-2CU-24S	390	2	7 x 32	Polyvinyl	Polyvinyl	105	221	2.1 x 3.4 (0.082 x 0.134)	5 (10)
	24	EXPP-3CU-24S	520	3	7 x 32	Polyvinyl	Polyvinyl	105	221	4.22 Ø (0.166 Dia.)	6 (14)

* Maximum temperature is for extension-grade wire or insulation, whichever is lower.

† Weight of spool and wire rounded to the next highest kg/lb (does not include packing material).

*** Can be welded. ††† Can also be red/gray.

Ordering Example: EXTT-3CU-26S-25, 25' spool of thermistor and RTD extension wire, 24 gage, stranded, polyvinyl insulation, \$650 x 0.0625 = \$41.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters