



Sound Meter with Data Logging SD Card

HHSL402SD



- ✓ Measures 30 to 130dB
- ✓ 2 GB SD Card Included
- ✓ Automatic Range Selections
- ✓ Real Time Data Logger
- ✓ Large Backlit LCD
- ✓ MAX/MIN Function
- ✓ Auto Power-Off
- ✓ RS232 Interface (Optional Cable)
- ✓ Data Logging Software (Optional)
- ✓ Hard Carrying Case Included

HHSL402SD

The HHSL402SD is a general-purpose handheld instrument that measures the noise level of an environment or the sound level produced by a piece of machinery. Using an integrated 13 mm (0.5") condenser microphone, the meter can measure sound levels from 30 to 130 dB with a resolution of 0.1 dB and show the results on a front-panel liquid-crystal display. Several features and capabilities enhance the meter's versatility. Among them are autoranging, the ability to hold readings and display maximum and minimum readings, and user-settable measurement parameters such

as frequency weighting (using the "A" and "C" standards) and time weighting (fast or slow). Because it is microprocessor-based, the HHSL402SD can make full use of the portability, reliability and large storage capacities that SD memory cards offer. Measurements can be made automatically at any sampling rate between one second and one hour. After timestamping and storing the measurements on an SD card plugged into the instrument, the user can remove the card and

plug it into a laptop or desktop computer either directly or via a USB card reader. The data points are stored on the card as files with the .xls extension, which can be opened by Microsoft's Excel application. The HHSL402SD has a backlit 64 mm (2.5") diagonal display and is powered by six "AA" alkaline batteries or an optional 9V AC/DC adaptor.





Sound wind shield ball.

All items included and shown smaller than actual size.

HHSL402SD

Hard carrying case.

2 GB SD card with case.

Specifications

Display Type: LCD with green backlight

Display Size: 52 x 38 mm (2.05 x 1.5")

Parameter Measured: dB

Frequency Range: 31.5 Hz to 8 kHz

Measurement Range:

- 30 to 130 dB in autoranging mode
- User can also select fixed range of 30 to 80 dB, 50 to 100 dB, or 80 to 130 dB

Measurement Weighting:

- **By Frequency:** Frequency weighing uses "A" or "C" standard
- **By Time:** Time weighting is fast or slow (200 or 500 ms response time)

Measurement Accuracy:

- With "A" frequency weighting:
 ± 3.5 dB @ 31.5 Hz, 2.5 dB @ 63 Hz,
 2 dB @ 125 Hz, 1.9 dB @ 250 Hz,
 1.9 dB @ 500 Hz, 1.4 dB @ 1 kHz,
 2.6 dB @ 2 kHz, 3.6 dB @ 4 kHz,
 5.6 dB @ 8 kHz

Measurement Resolution: 0.1 dB

Data Logging Sampling Time:

1 second to 1 hour

Settable Parameters: Date, time, auto power off, beep sound, sampling time, decimal point or comma decimal division, "A" or "C" frequency weighting, fast or slow time weighting

Storable/Recallable Readings:

Maximum, minimum

SD Card Capacity: 1 to 16 GB

Operating Temperature: 0 to 50°C (32 to 122°F)

Operating Relative Humidity: 0 to 85%

Power Supply: Six alkaline "AA" batteries or optional 9 Vdc AC adaptor

Power Consumption:

- 8 mADC (normal operation, with backlight off and SD card not saving data)
- 30 mADC with backlight on and card saving data
- 44 mADC with backlight on and card saving data

Dimensions of Meter:

245 x 68 x 45 mm (9.65 x 2.68 x 1.77")

Weight of Meter: 489 g (1.08 lbs)



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

To Order Visit omega.com/hhsl402sd for Pricing and Details

| Model No. | Description |
|-----------|---------------------------------------|
| HHSL402SD | Sound meter with data logging SD card |

Accessories (Field Installable)

| Model No. | Description |
|-------------|--|
| 2GB-SD | Spare 2 GB SD card |
| ADAPTER-SD | AC power adaptor |
| SW-U101-WIN | Software for data logging with RS232 cable |
| RS232-SD | Optional RS232 interface cable |

Comes complete with sound wind shield ball, 6 "AA" batteries, hard carrying case, 2 GB SD memory card, and operator's manual.

Ordering Example: HHSL402SD, sound meter with data logging SD card.

OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters