

NEMA 4X Thermostats for Heat Tracing Applications

HT-110 Series
Starts at
\$321



- ✓ Adjustable Temperature Ranges
- ✓ Rugged Die Cast Aluminum Enclosure
- ✓ Terminal Block Wiring
- ✓ 22 Amp SPDT Switch Output

The OMEGA® HT-110 Series was designed to meet the demanding temperature requirements of the power and process industries. The NEMA 4X gasketed, die-cast aluminum epoxy coated enclosure is weather tight and corrosion resistant. The externally calibrated, tamper resistant adjustment dial is calibrated in degrees Fahrenheit and Celsius and allows easy access for temperature control settings.

Specifications

Bulb and Capillary (HT-111):

3 m (10') liquid filled SS

Stem Material (HT-113):

Stainless steel

Storage Temperature:

-55 to 70°C (-67 to 158°F)

Ambient Temperature Limits:

-40 to 70°C (-40 to 158°F)

Electrical Rating:

22 A @ 480 Vac

Switch: SPDT, switch may be wired normally open or normally closed

Electrical Connector: ½ NPTF, terminal block standard

Temperature Deadband:

2% of range*

* Under laboratory conditions.



HT-111, \$380, shown smaller than actual size.

HT-113, \$321, shown smaller than actual size.



CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel.

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)							
Model Number	Price	Temp Range °C (°F)	Amperage Rating	Bulb Size OD X L	Stem Size OD X L	Dial Div. °C/°F	Wt. kg (lb)
HT-113	\$321	-10 to 60 (14 to 140)	22 A	-	14.2 x 68.3 mm (0.56 x 2.69")	2/2	1 (2)
HT-111	380	-5 to 160 (23 to 320)	22 A	3.3 x 295.4 mm (0.13 X 11.63")	-	5/5	1.4 (3)

Comes with complete operator's manual.
Ordering Example: HT-113, NEMA 4X (IP65) thermostat, \$321.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters