

Transition Junction Style Probes

With High Temperature Molded Construction

Standard Dimensions

- ✓ 6 and 12" Lengths in Stock†
- ✓ Sheath Diameters from 0.010 to 0.125"
- ✓ 304SS, 310SS, 316SS, 321SS, Inconel® or Super OMEGACLAD® XL Sheath
- ✓ Grounded, Ungrounded or Exposed Junction
- ✓ 40" PTFE-Coated Lead Wires Standard
- ✓ Environmentally Friendly Cadmium-Free Liquid Crystal Polymer
- ✓ Molded Transition Junction Rated to 260°C (500°F)

Available in Type N Calibration

MEETS OR EXCEEDS SPECIAL LIMITS OF ERROR (SLE) AND EN 60584-2: Tolerance Class 1

MADE IN USA OMEGACLAD Factory CAL AVAILABLE

Available as



ANSI color code shown To order IEC color code visit omega.com

SUPER OMEGACLAD® XL THERMOCOUPLE WIRE
MAXIMUM PERFORMANCE SHEATHING ELIMINATES HIGH TEMPERATURE DRIFT

See omega.com

Discount Schedule

1-10 Units.....	Net
11-24 Units.....	10%
25-49 Units.....	20%
50 and Up.....	Consult Sales



To Order Visit omega.com/jmtss for Pricing and Details			
ANSI Color Code/Alloy	Sheath Dia. in.	Model No. 6" Length	Model No. 12" Length
J Iron-Constantan 304 SS Sheath	0.010"	JMTSS-010(*)-6	JMTSS-010(*)-12
	0.020"	JMTSS-020(*)-6	JMTSS-020(*)-12
	0.032"	JMTSS-032(*)-6	JMTSS-032(*)-12
	0.040"	JMTSS-040(*)-6	JMTSS-040(*)-12
	0.062"	JMTSS-062(*)-6	JMTSS-062(*)-12
	0.125"	JMTSS-125(*)-6	JMTSS-125(*)-12
**K CHROMEQA®-ALOMEGA® 304 SS Sheath	0.010"	KMTSS-010(*)-60	KMTSS-010(*)-12
	0.020"	KMTSS-020(*)-6	KMTSS-020(*)-12
	0.032"	KMTSS-032(*)-6	KMTSS-032(*)-12
	0.040"	KMTSS-040(*)-6	KMTSS-040(*)-12
	0.062"	KMTSS-062(*)-6	KMTSS-062(*)-12
	0.125"	KMTSS-125(*)-6	KMTSS-125(*)-12
E CHROMEQA®-Constantan 304 SS Sheath	0.010"	EMTSS-010(*)-6	EMTSS-010(*)-12
	0.020"	EMTSS-020(*)-6	EMTSS-020(*)-12
	0.032"	EMTSS-032(*)-6	EMTSS-032(*)-12
	0.040"	EMTSS-040(*)-6	EMTSS-040(*)-12
	0.062"	EMTSS-062(*)-6	EMTSS-062(*)-12
	0.125"	EMTSS-125(*)-6	EMTSS-125(*)-12
T Copper-Constantan 304 SS Sheath	0.020"	TMTSS-020(*)-6	TMTSS-020(*)-12
	0.032"	TMTSS-032(*)-6	TMTSS-032(*)-12
	0.040"	TMTSS-040(*)-6	TMTSS-040(*)-12
	0.062"	TMTSS-062(*)-6	TMTSS-062(*)-12
	0.125"	TMTSS-125(*)-6	TMTSS-125(*)-12

Note: Probes with 0.040" diameter and larger supplied with molded transition joints. Smaller-size probes supplied with stainless steel transition joints. All Type N probes supplied with stainless steel transition joints; see omega.com for Type N probe pricing and information.

*Specify junction type: **E** (exposed), **G** (grounded) or **U** (ungrounded). †Other lengths available, please consult Sales Department.

To order with 304, 310, 316 or 321 SS sheath, change "SS" in model number to "304SS", "310SS", "316SS" or "321SS" respectively; no additional charge. Consult Sales for lengths between 2 to 12", or for lengths over 24". Type N Inconel Sheathing is available, Contact Sales for model numbers.

**For Super OMEGACLAD® XL, change "SS" to "XL" and add additional cost to the price.

Ordering Example: KMTSS-125U-6, subminiature transition joint probe, Type K, 0.125" O.D. 304 stainless steel sheath, 6" length, ungrounded junction.

Transition Junction Style Probes

With High Temperature Molded Construction

Metric Dimensions

- 150 mm and 300 mm Lengths in Stock†
- 1 m PTFE-Coated Lead Wires Standard
- Sheath Diameters from 0.25 mm to 3.0 mm
- 304SS, 310SS, 316SS, 321SS, Inconel® or Super OMEGACLAD® XL Sheath
- Grounded, Ungrounded or Exposed Junction
- Environmentally Friendly Cadmium-Free Liquid Crystal Polymer
- Molded Transition Junction Rated to 260°C (500°F)

MEETS OR EXCEEDS SPECIAL LIMITS OF ERROR (SLE) AND EN 60584-2: Tolerance Class 1

MADE IN USA OMEGACLAD® Factory CAL AVAILABLE


Available in Type N Calibration

ANSI color code shown


To order IEC color code visit omega.com

Available as **SUPER OMEGACLAD® XL THERMOCOUPLE WIRE** MAXIMUM PERFORMANCE SHEATHING ELIMINATES HIGH TEMPERATURE DRIFT

See omega.com



Discount Schedule	
1-10 Units.....	Net
11-24 Units.....	10%
25-49 Units.....	20%
50 and Up.....	Consult Sales



To Order Visit omega.com/jmtss for Pricing and Details

ANSI Color Code/Alloy	Sheath Dia. mm	Model No. 150 mm Length	Model No. 300 mm Length
J Iron-Constantan 304 SS Sheath	0.25	JMTSS-M025(*)-150	JMTSS-M025(*)-300
	0.50	JMTSS-M050(*)-150	JMTSS-M050(*)-300
	0.75	JMTSS-M075(*)-150	JMTSS-M075(*)-300
	1.0	JMTSS-M100(*)-150	JMTSS-M100(*)-300
	1.5	JMTSS-M150(*)-150	JMTSS-M150(*)-300
	3.0	JMTSS-M300(*)-150	JMTSS-M300(*)-300
**K CHROMEQA®-ALOMEGA® 304 SS Sheath	0.25	KMTSS-M025(*)-150	KMTSS-M025(*)-300
	0.50	KMTSS-M050(*)-150	KMTSS-M050(*)-300
	0.75	KMTSS-M075(*)-150	KMTSS-M075(*)-300
	1.0	KMTSS-M100(*)-150	KMTSS-M100(*)-300
	1.5	KMTSS-M150(*)-150	KMTSS-M150(*)-300
	3.0	KMTSS-M300(*)-150	KMTSS-M300(*)-300
E CHROMEQA® Constantan 304 SS Sheath	0.25	EMTSS-M025(*)-150	EMTSS-M025(*)-300
	0.50	EMTSS-M050(*)-150	EMTSS-M050(*)-300
	0.75	EMTSS-M075(*)-150	EMTSS-M075(*)-300
	1.0	EMTSS-M100(*)-150	EMTSS-M100(*)-300
	1.5	EMTSS-M150(*)-150	EMTSS-M150(*)-300
	3.0	EMTSS-M300(*)-150	EMTSS-M300(*)-300
T Copper-Constantan 304 SS Sheath	0.50	TMTSS-M050(*)-150	TMTSS-M050(*)-300
	0.75	TMTSS-M075(*)-150	TMTSS-M075(*)-300
	1.0	TMTSS-M100(*)-150	TMTSS-M100(*)-300
	1.5	TMTSS-M150(*)-150	TMTSS-M150(*)-300
	3.0	TMTSS-M300(*)-150	TMTSS-M300(*)-300

Note: Probes with 1.0 mm diameter and larger supplied with molded transition joints. Smaller-size probes supplied with stainless steel transition joints. All Type N probes supplied with stainless steel transition joints; see omega.com for Type N probe pricing and information.

*Specify junction type: **E** (exposed), **G** (grounded) or **U** (ungrounded) †Other lengths available, consult Sales Department
To order with 304, 310, 316 or 321 SS sheath, change "SS" in model number to "304SS", "310SS", "316SS" or "321SS" respectively; no additional charge. Consult Sales for lengths between 2 to 12" or for lengths over 24" **Type N Inconel Sheathing is available**, Contact Sales for model numbers.
****For Super OMEGACLAD® XL**, change "SS" to "XL" and add additional cost to the price.

Ordering Example: KMTSS-M150G-150, subminiature transition joint probe, Type K, 1.5 mm O.D. stainless steel sheath, 150 mm length, grounded junction.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters