


# Linear Tubular Glass Thermistor Sensors For Immersion Temperature Measurements

OL-704, \$185, shown smaller than actual size.



Dimensions: mm (in)

OL-704  
\$185



- ✓ Chemically Inert for Liquid Immersion Use
- ✓ Can be Used for Thermal Titration Studies and Measurement of Freezing Points
- ✓ Comes with a 127 mm (5") Long Pyrex Probe and 3 m (10') of PVC Cable with Phone Plug Connector

**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)					
Model Number	Price	Sensor Type	Thermistor Model Number	Resistance #1 @ 25°C	Resistance #2 @ 25°C
OL-704	\$185	Tubular glass	immersion sensor	44018	6000 Ω

## Optional Resistor Sets

Model Number	Price	Description	Resistor R1	Resistor R2
44301	\$12	Resistor set	3200 Ω	6250 Ω
44302	12	Resistor set	5700 Ω	12000 Ω
44303	12	Resistor set	18700 Ω	35250 Ω
44304	12	Resistor set	5700 Ω	12400 Ω

**Note:** See page Z-256 for additional resistance vs. temperature information.

**Options:** Add optional resistor sets shown above for linearizing the sensor output based on your specific requirements (see pages D-35 through D-36).

**Ordering Example:** OL-704, linear tubular glass immersion sensor, 3 m (10') of PVC insulated and jacketed cable with phone plug connector, \$185

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters