



Smart Loop-Powered RTD In-Head Temperature Transmitter

TX12
£33.50



- ✓ User Trim—Null Out Sensor Error
- ✓ Unique Push Button Configuration Without PC
- ✓ High Stability
- ✓ Programmable Burnout
- ✓ LED Sensor Fail Indicator
- ✓ Reconfigure in Seconds

The TX12 head mounted temperature transmitter connects to any standard Pt100 resistance sensor and converts the linearised temperature to a 4 to 20 mA signal. The transmitter is a two wire device, and is fully configurable by the user, over a wide temperature range, with the aid of a simple push button. This new TX12 design incorporates additional configuration menus, allowing the user to push button trim the transmitter output at both zero and span, ideal for trimming out sensor errors. The transmitters advanced circuitry ensures high stability over the wide operating ambient temperature ranges experienced by head mounted devices.

One of the transmitters features is the program LED, which provides visual indication of sensor fault when in normal operation and is also used to guide the operator through the simple menus during configuration.

Specifications Input

Sensor Type: Pt100 100R @ 0°C
2 or 3 Wire
Sensor Range: -200 to 850°C
(-18 to 390°F) ø
Sensor Connection: Screw terminal
Minimum Span: 25°C (77°F)
Linearisation: BS EN 60751(IEC 751) standard/JISC 1604
Measurement Accuracy: 0.1°C
±0.05% of reading
Thermal Drift: 25 ppm/°C
Excitation Current: <200 uA

Lead Resistance Effect: 0.002°C/
Maximum Lead Resistance:
20 per leg

Output

Output Type: 2 wire, 4 to 20 mA current loop
Output Range: (4.0 to 20.0) mA
Output Connection: Screw terminal
Maximum Output: 21.5 mA (in high burnout condition)
Minimum Output: 3.8 mA (in low burnout condition)
Accuracy: (mA output /2000) or 5 uA (whichever is the greater)

Loop Voltage Effect: 0.2 uA/V

Thermal Drift: 1 uA /°C

Maximum Output Load:
[(Vsupply-10)/20]K
(Example: 700 @ 24V)

General Specifications

Update Time: 500 mS
Response Time: 1 second
Start Up Time: 4 seconds
(I out < 4 mA during start up)
Warm-Up Time: 1 minute to full accuracy
Power Supply: 10 to 30 Vdc

Environmental

Ambient Operating Range: -40 to 85°C
(-40 to 185°F)
Ambient Storage Temperature:
-50 to 90°C (-58 to 194°F)
Ambient Humidity Range: 10 to 90% RH non condensing



TX12, £33.50, shown larger than actual size.

Physical

Dimensions: 43 mm diameter; 21 mm height (1.7"; 0.8")
Weight: 31 g (0.068 lb) (encapsulated)

Approvals

EMC - BS EN 61326 :1998:
Electrical equipment for measurement control and laboratory use
ANNEX A: Immunity test requirements for equipment intended for use in industrial locations
ANNEX F: Test configurations, operational conditions and performance criteria for transducers with integrated or remote signal conditioning
IEC 61000-4-2: Electrostatic discharge
IEC 61000-4-3: EM field
IEC 61000-4-4: Transient burst (output)
IEC 61000-4-5: Surge (output)
Note: Sensor input wires to be less than 3 m to comply.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
TX12	£33.50	RTD transmitter (Pt100)
TX2-100	19.00	2-core screened cable, 30 metre reel
PSR-24L-230-UK	40.20	Regulated power supply, 24 Vdc, 400 mA, stripped leads, 230 Vac input. 3 pin UK Plug
PSR-24L-230	40.20	Regulated power supply, 24 Vdc, 400 mA, stripped leads, 230 Vac input. 2 pin Euro Plug
TX-SCALED	30.00	Scaling charge for factory set up of range (specify temperature range)

Comes with operator's manual.

Ordering Example: TX12, RTD transmitter and PSR-24L-230-UK, regulated power supply with stripped leads, £33.50 + 40.20 = £73.70.

N



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters